
DATA SHEET



790MM ACTIVESMART™ FRIDGE

Model no:

RF170BRPUX6

(refer page 2 for metric measurements)

Product Dimensions	in
Overall height* of fridge	67 3/4"
Overall width of fridge	31 1/8"
© Depth of fridge door and gasket	2 3/4"
Depth of fridge door and chassis	27 3/8"
© Depth of fridge chassis (does not include fridge door)	24 5/8"
F Height of feet (adjustable)	15/16"
Height from bottom of chassis to bottom of bottom door	5/8"
Height from bottom of chassis to top of bottom door	24 5/8"
① Gap between doors	3/8"
Height of top door	41 3/4"
Depth of door gasket	9/16"
Depth of evaporator tray behind chassis	1 3/16"
Depth of door (open at 90°) (measured from front of door)	29 5/16"
Rotation of door (open)	138°
* Includes mounted feet	

Minimum Clearances	
Minimum height of cavity	68 5/16"
Minimum side clearance installed flush with chassis	13/16"
Side clearance (hinge side) installed flush with door - full rotation	5 5/16"
Rear clearance (including evaporator tray)	1 3/16"


INDICATES PRODUCT DATUM ------INDICATES CABINETRY CLEARANCES ------

DATE: 12.12.2016

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ± 2 mm (3/32"). Please read the installation manual for detailed information on installing the product. www.fisherpaykel.com



DATA SHEET



790MM ACTIVESMART™ FRIDGE

Model no:

RF170BRPUX6

(refer page 1 for imperial measurements)

Product Dimensions	mm
Overall height* of fridge	1720
Overall width of fridge	790
© Depth of fridge door and gasket	70
Depth of fridge door and chassis	695
© Depth of fridge chassis (does not include fridge door)	625
Height of feet (adjustable)	24
Height from bottom of chassis to bottom of bottom door	16
(H) Height from bottom of chassis to top of bottom door	626
① Gap between doors	10
① Height of top door	1060
® Depth of door gasket	15
© Depth of evaporator tray behind chassis	30
® Depth of door (open at 90°) (measured from front of door)	745
® Rotation of door (open)	138°
* Includes mounted feet	
Minimum Clearances	mm

Minimum Clearances	mm
Minimum height of cavity	1735
Minimum side clearance installed flush with chassis	20
Side clearance (hinge side) installed flush with door - full rotation	135
Rear clearance (including evaporator tray)	30

INDICATES PRODUCT DATUM ------INDICATES CABINETRY CLEARANCES ------

DATE: 12.12.2015

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ± 2 mm (3/32"). Please read the installation manual for detailed information on installing the product. www.fisherpaykel.com

