

600mm Integrated Double DishDrawer™ Tall

Model no:

DD24DTI7 (refer page 2 for imperial measurements)

DD24DHTI7

Product Dimensions	mm
Ⓐ Overall height* of DishDrawer™	864 - 924
Ⓑ Overall width** of DishDrawer™	599
Ⓒ Depth of DishDrawer™ chassis**	553
Ⓓ Minimum height from top datum to bottom of bottom drawer	767
Ⓔ Height from top datum to top of bottom drawer	456
Ⓕ Minimum height from top datum to bottom of top drawer	448
Ⓖ Ventilation gap between custom panels	8
Ⓜ Minimum height of lower drawer panel	311
Ⓣ Height of chassis at rear (not including mounted feet)	855
Ⓟ Height of mounted feet (adjustable)	9 - 69
ⓧ Height of toekick custom panel (adjustable)	70 - 120
Ⓛ Depth of toekick panel*** (adjustable)	30 - 85
Ⓜ Depth of drawer (open) (measured from front datum)**	527

* Includes adjustable mounted feet and the range of movement.

** Does not include the custom drawer panels, handles or toekick panel to be manufactured and fitted by cabinetmaker.

*** Does not include the custom toekick panel to be manufactured and fitted by cabinetmaker. If the toekick depth is greater than 50mm, the panel will need to be cut to clear the underside of the tub, please refer to the installation manual for more detail.



Note: Service outlet at rear extends both sides, hoses and cords can be routed to either or both.

Minimum Clearances	mm
Minimum inside height of cavity from bottom datum	864
Minimum inside width of cavity	600
Minimum inside depth of cavity from front datum	560
Minimum ventilation gap between custom panels	8
Minimum clearance from underside of bench to top of custom panel	2
Minimum clearance from bottom of toekick panel to floor	12

INDICATES CABINETRY CARCASS DATUM -----
INDICATES MINIMUM CABINETRY CLEARANCES - - - - -

DATE: **05.05.2014**

IMPORTANT NOTE: Throughout this guide, dimensions may vary by $\pm 2\text{mm}$ (3/32"). Please read the installation manual for detailed information on installing the product. www.fisherpaykel.com



24" Integrated Double DishDrawer™ Tall

Model no:

DD24DT17 (refer page 1 for metric measurements)

DD24DHT17

Product Dimensions	in
Ⓐ Overall height* of DishDrawer™	34- ¹ / ₃₂ " - 36- ⁵ / ₁₆ "
Ⓔ Overall width of DishDrawer™	23- ¹⁹ / ₃₂ "
Ⓒ Depth of DishDrawer™ chassis**	21- ²⁵ / ₃₂ "
Ⓓ Minimum height from top datum to bottom of bottom drawer	30- ³ / ₃₂ "
Ⓔ Height from top datum to top of bottom drawer	17- ¹⁵ / ₁₆ "
Ⓓ Minimum height from top datum to bottom of top drawer	17- ⁵ / ₁₆ "
Ⓔ Ventilation gap between custom panels	⁵ / ₁₆ "
Ⓔ Minimum height of lower drawer panel	12- ¹ / ₄ "
Ⓒ Height of chassis at rear (not including mounted feet)	33- ²¹ / ₃₂ "
Ⓒ Height of mounted feet (adjustable)	1 ¹ / ₂ " - 2- ²³ / ₃₂ "
Ⓒ Height of toekick custom panel (adjustable)	2- ³ / ₄ " - 4- ²³ / ₃₂ "
Ⓒ Depth of toekick panel***(adjustable)	1- ³ / ₁₆ " - 3- ¹ / ₃₂ "
Ⓒ Depth of drawer (open) (measured from front datum)**	20- ³ / ₄ "

* Includes adjustable mounted feet and the range of movement.

** Does not include the custom drawer panels, handles or toekick panel to be manufactured and fitted by cabinetmaker.

*** Does not include the custom toekick panel to be manufactured and fitted by cabinetmaker. If the toekick depth is greater than 1-³/₃₂", the panel will need to be cut to clear the underside of the tub, please refer to the installation manual for more detail.

Note: Service outlet at rear extends both sides, hoses and cords can be routed to either or both.

Minimum Clearances	in
Minimum inside height of cavity from bottom datum	34- ¹ / ₃₂ "
Minimum inside width of cavity	23- ⁵ / ₁₆ "
Minimum inside depth of cavity from front datum	22- ¹ / ₁₆ "
Minimum ventilation gap between custom panels	⁵ / ₁₆ "
Minimum clearance from underside of bench to top of custom panel	³ / ₃₂ "
Minimum clearance from bottom of toekick panel to floor	1 ⁵ / ₃₂ "

INDICATES CABINETRY CARCASS DATUM

INDICATES MINIMUM CABINETRY CLEARANCES

DATE: 05.05.2014

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (3/32"). Please read the installation manual for detailed information on installing the product. www.fisherpaykel.com

Fisher & Paykel