FISHER & PAYKEL

DATA SHEET

Steam Oven

Model no:

OS30NPX1

(refer page 2 for metric measurements)


Product Dimensions	inch
Overall height of product	18 1/2
Overall width of product	29 13/16
© Overall depth of product (excluding handle)	22 5/16
Height of chassis	17 9/16
© Width of chassis	25 7/16
© Depth of chassis	20 13/16
© Depth of oven front frame and control panel (excludes handle)	1 9/16
Depth of oven door when fully open (measured from front of control panel)	12 1/8
① Height from top of control panel to top of chassis	9/16
① Height from bottom of chassis to bottom of lower trim	7/16
Height of control panel	3 15/16
© Height from bottom of chassis to centreline of handle	12 7/8

Minimum Clearances	inch
Minimum inside height of cavity from base of chassis*	17 3/4
Minimum cavity width	25 3/8
Minimum inside cavity depth from front of chassis**	22 1/16
Rear ventilation depth***	2
Rear ventilation width***	22 1/16

 * A spacer may be required in the base of the cavity. For more information on clearances, refer to installation guide.

**Flush Installation possible. Depending on cabinet panel thickness a rebate around front frame might be required, refer to installation guide.

***Rear ventilation totalling 43.4in² is required. The air vent must be located at the rear of cabinet, it can be positioned at the base, sides, back or top of the cavity.



0

•

PLAN VIEW

POWER LOCATION

DATUM: FRONT OF CHASSIS


INDICATES CABINETRY / PRODUCT DATUM ------INDICATES CABINETRY CLEARANCES ------

DATE: 10.10.2023

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ± 2 mm (1/16"). Please read the installation guide for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com



DATUM: FRONT OF CHASSIS PLAN VIEW



DATUM : FRONT OF CHASSIS

FISHER & PAYKEL

DATA SHEET

Steam Oven

Model no:

OS30NPX1

(refer page 1 for imperial measurements)

Product Dimensions	mm
Overall height of product	470
® Overall width of product	757
© Overall depth of product (excluding handle)	567
Height of chassis	446
© Width of chassis	645
© Depth of chassis	528
Depth of oven front frame and control panel (excludes handle)	39
Depth of oven door when fully open (measured from front of control panel)	308
① Height from top of control panel to top of chassis	14
① Height from bottom of chassis to bottom of lower trim	10
Height of control panel	100
U Height from bottom of chassis to centreline of handle	327

mm
450
645
560
50
560

^{*}A spacer may be required in the base of the cavity. For more information on clearances, refer to installation guide.

INDICATES CABINETRY / PRODUCT DATUM ------INDICATES CABINETRY CLEARANCES ------

DATE: 10.10.2023

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ± 2 mm (1/16"). Please read the installation guide for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com

^{**}Flush Installation possible. Depending on cabinet panel thickness a rebate around front frame may be required, refer to installation guide.

^{***}Rear ventilation totalling 280cm² is required. The air vent must be located at the rear of cabinet, it can be positioned at the base, sides, back or top of the cavity.